

Characteristics



Activated Carbon



Corrosive Recovery



Pharma Applications



Cleanroom Compatible



Accessories Included



Wear Protective Clothing (PPE)



- Cleanroom compatible with ISO Class 4 (former Class 10). Can be used in the Pharmaceutical industry when equipped with stainless steel Type 304 4-wheel dolly or tilting cart
- Designed for the recovery of acids and corrosive liquids
- To be used as a Recovery Unit in conjunction with a vacuum system
- Available with a variety of activated carbon, including KINA 3® activated carbon for the adsorption of chloride and acid vapors (HF, HCL, etc). Other types of activated carbon are available. Carbon cartridges must be ordered separately - not included
- For liquid recovery
- Acid-resistant polyethylene, nylon and PVC
- Available with a 4-wheel dolly, tilting cart, or hydro-cart
- 4-wheel dolly, and tilting cart available in stainless steel
- Includes a complete tool kit.

Specifications

ARU-15 CR/STD SERIES	211860	211862	211863	211864	211865	211866
Model Name	ARU-15 STD (4W)	ARU-15 CR (4W)	ARU-15 STD (HY-C) MRAC	ARU-15 STD (4W) MRAC	ARU-15 CR (4W) MRAC	ARU-15 STD (TC) MRAC
Suction Inlet Port	38 mm	38 mm	38 mm	38 mm	38 mm	38 mm
Cart Type	4 Wheel Dolly (4W)	4 Wheel Dolly (4W)	Hydro Cart (HYC)	4 Wheel Dolly (4W)	4 Wheel Dolly (4W)	Tilt Cart (TC)
Filter Cleaning	None	None	None	None	None	None
Liquid Recovery Capacity	47.3 L	47.3 L	47.3 L	47.3 L	47.3 L	47.3 L
ARU-15 CR/STD SERIES	211870	211874	211878			
Model Name	ARU-15 STD (TC)	ARU-15 CR (TC)	ARU-15 CR (TC) MRAC			
Suction Inlet Port	38 mm	38 mm	38 mm			
Cart Type	Tilt Cart (TC)	Tilt Cart (TC)	Tilt Cart (TC)			
Filter Cleaning	None	None	None			
Liquid Recovery Capacity	47.3 L	47.3 L	47.3 L			

Please note that specifications are subject to change without notice

Use only recommended tools & accessories



ARU STD Tools and Accessories - Included



Liquid Filter - Included



Activated Carbon Cartridge - Optional