

## Characteristics




Dry Recovery



EX Certified



Pharma  
Applications



Less than 10  
ohms



Stainless  
General



- High/Low Pressure Hopper
- High quality stainless steel Type 304 construction and compatible with the Pharmaceutical and Food industries
- Less than 10 ohms of resistivity
- Unit is equipped with a heavy duty powder coated stand
- The suction intake and the connection to the power source are Ø4" (Ø100 mm) in size
- An Ø8" (200 mm) gate valve is included
- The following filtration systems are available depending on the type of material being recovered: 1) Manual Filter Shaker (MFS) with bell shaped conductive cloth media with a large surface area 2) Manual Reverse Purge (MRP) with conductive spun bond cartridge 3) Automatic Reverse Purge (ARP) with controls/timers with conductive spun bond cartridge
- Suction and connection hoses for the Pharmaceutical and Food industries are available
- Available with a recovery drum of 40 gal. (16L), recovery drum on a pallet, or Super Bulk Bag on a pallet

## Specifications

HOPPER FRS-570 SS	112326
<b>Model Name</b>	HOPPER FRS-570 SS
<b>Suction Inlet Port</b>	102 mm
<b>Cart Type</b>	None
<b>Filter Cleaning</b>	None

Please note that specifications are subject to change without notice

### Use only recommended tools & accessories



Gate Valve 8" - Included